




Front locking devices

Front locking devices - Standard mount - Side and depth adjustments

For all Progressa, Progressa+ and Progressa+ Shelf slides

- Dual steel/fiber glass-nylon construction
- Compatible with all Progressa slides
- Tool free lateral and depth adjustments
- Pre-drilling recommended \varnothing 2.5 mm (3/32")




AFCGXX3B


PACKAGING

2 boxes = 100 pcs right and 100 pcs left

Assembly to the bottom



Assembly to the drawer




Use **drilling templates** for accurate installation of the clips, see page 62.

Front locking devices - Standard mount - Front and side fixing

For all Progressa, Progressa+ and Progressa+ Shelf slides

- Engineered thermoplastics
- Compatible with all Progressa slides
- Side fixing option
- Pre-drilling recommended \varnothing 2.5 mm (3/32")
- Minimum inside drawer width 5-1/8"
- Minimum inside cabinet width 6-3/4"




AFCEX56B


PACKAGING

2 boxes = 100 pcs right and 100 pcs left

Assembly to the bottom



Assembly to the drawer




Use **drilling template** for accurate installation of the clips, see page 65.

Drawer removal

Standard and vertical mount - 6-way adjustable - Side and depth adjustments

For all Progressa, Progressa+ and Progressa+ Shelf slides

Position hands under the front of the drawer and press on the orange levers, as indicated in the drawing, sliding the drawer out of the cabinet.



Standard mount - 2-way adjustable - Front and side fixing

For all Progressa, Progressa+ and Progressa+ Shelf slides

Position hands under the front of the drawer and press on the black levers, as indicated in the drawing, sliding the drawer out of the cabinet.

